

Technical data sheet

Trunking unit, blank, height 100–150 mm

Item number: 7424444



Ready-to-mount trunking unit with three blanking lids for cable laying, consisting of the trunking base (floor trough with side and floor covering contact profiles) and trunking lid. Floor trough with holding straps for self-contacting mounting of separating retainers. The scope of delivery contains 6 height-adjustable fixing brackets, 6 screed anchors and lid butt seals (3x for nominal trunking widths of 200 and 300) or height-adjustable lid butt supports: 3x for nominal trunking width 400 and 6x for nominal trunking widths 500 and 600. Trunking lid screwed on for delivery.



St

Steel

FS

Strip galvanised

Master data

Item number	7424444
Type	OKA-W40010050
Description 1	Flushfloor trunking unit
Description 2	blank
Manufacturer	OBO
Dimension	2400x400x100
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	2.4
Unit of quantity	Metre
Weight	1879.2 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	75,6137 kg CO2e / 1 Meter

Dimensions



Length	2,400 mm
Width	400 mm

Technical data sheet

Trunking unit, blank, height 100–150 mm

Item number: 7424444



Technical data

Mounting opening cover	no
Covers	3
Number of mounting openings	0
Number of insertable partitions	2
Number of planned flush-mount units	3
Number of compartments	3 St.
Mounting system fastening type	Floor
Floor plate	yes
Cover fastening, locking	no
Seal installation option	yes
Installation opening for on-floor tank	no
Decouplable	no
Suitable for expansion joint	no
Mesh wall	no
Trunking height, max.	150 mm
Duct height, min.	100 mm
Cover material thickness	4
Minimum screed height	100
With connection opening	no
With equipotential bonding	no
With separating retainer	no
With overhang	yes
Mounting opening	Without
Height-adjustment range, max.	150 mm
Height-adjustment range, min.	100 mm
Usable cross-section	24100 mm ²
Removable cover	yes
ROHS-conformant	yes
Separating retainer fastening	rasten
Separating retainer fastening	Lock