

Technical data sheet

Floor box UDHOME9 with brush bar, stainless steel, with
FLF support, cover can be covered
Item number: 7427332



Square installation unit for use in dry-care cavity and screed floors for indoor use.

Installation housing with pre-marked insertion openings for pipes (M25). Cover adjustable to the top edge of the floor covering using four height-adjustment supports. The minimum installation depth is 95 mm, the height adjustment range is +30 mm.

Flushfloor cable outlet through brush bar.

Device support made of galvanised sheet steel for 9x FLF 3/5.

Lid can be covered with floor covering, 15 mm.

A2 Stainless steel

Master data

Item number	7427332
Type	UDHOME9 2V U PE
Description 1	Floor box, complete
Description 2	for FLF devices
Manufacturer	OBO
Material	Stainless steel 1.4301
Smallest sales unit	1
Unit of quantity	Piece
Weight	530 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	24,883 kg CO2e / 1 Piece


Technical data sheet

Floor box UDHOME9 with brush bar, stainless steel, with FLF support, cover can be covered

Item number: 7427332



Dimensions



Length	246 mm
Width	246 mm

Technical data

Cable outlet version	Brush bar
Equipment	FLF supports
Cover version	Floor covering recess
Screed height, max.	110 mm
Screed height, min.	95 mm
Floor height, max.	125 mm
Floor height, min.	95 mm
Length of external dimensions	243 mm
Length of installation dimensions	246 mm
Height-adjustment range, max.	125 mm
Height-adjustment range, min.	95 mm
ROHS-conformant	Exempt
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK10
Vertical load, large area	to 5,000 N
Vertical load, small area	to 3,000 N
Floor covering thickness	15 mm