


Technical data sheet

Complete solution, GES4 service outlet

Item number: 7427460



Square installation unit with cord outlet for use in dry-care cavity floors and screed floors for indoor use, consisting of an installation housing and GES4-2 service outlet (colour Iron grey; RAL 7011) with two universal supports. Installation housing with pre-marked insertion openings for pipelines (M25), adjustable to top edge of screed. In the as-delivered state, the installation housing is closed with a blanking lid. After screed work, the service outlet can be inserted in the created mounting opening. 3, 5, 8 or 10 mm floor covering recess in the hinged cover of the service outlet.

The minimum installation depth is 72 mm including floor covering, the height adjustment range +30 mm.

Up to 6 individual Modul 45® devices can be installed.



PA Polyamide

Master data

Item number	7427460
Type	GES4-2 BOX 7011
Description 1	Service outlet-Set
Description 2	with mounting boxes
Manufacturer	OBO
Dimension	222x222x140
Colour	Iron grey; RAL 7011
Material	Polyamide
Smallest sales unit	1
Unit of quantity	Piece
Weight	290 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	9,9593 kg CO2e / 1 Piece


Technical data sheet

Complete solution, GES4 service outlet


Item number: 7427460



Dimensions



Length	205 mm
Width	205 mm



Technical data

Cable outlet version	Swivellable cord outlet
Screed height, max.	100 mm
Screed height, min.	80 mm
ROHS-conformant	Exempt
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK08
Installation system type	UT3
Opening mechanism	Locking slider
Floor covering thickness	5 mm