

Technical data sheet

Trunking RFT 225 unit with cable outlet M25

Item number: 7428193



The raised floor trunking can be used for routing cables underneath raised floor panels. Retaining straps permit the self-contacting mounting of separating retainers.

Included in the delivery are one trunking base, four trunking covers and eight locking brackets. Two trunking covers have three M25 pipe entry openings. Two trunking covers are completely closed. Separating retainers should be ordered separately.



St	Steel
FS	Strip galvanised

Master data

Item number	7428193
Type	RFT 225 40
Description 1	Raised floor trunking
Description 2	with cover
Manufacturer	OBO
Dimension	2400x225x40
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	1019.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	25,1387 kg CO2e / 1 Piece


Technical data sheet

Trunking RFT 225 unit with cable outlet M25

Item number: 7428193



Dimensions



Length	2,400 mm
Width	225 mm
Height	40 mm
Plate thickness	1 mm
Dimension b	225 mm
Dimension h	40 mm

Technical data

Number of compartments	3 St.
Floor plate	yes
Cover fastening, locking	yes
Seal installation option	no
Installation opening for on-floor tank	no
Decouplable	no
For pipe connection	yes
Suitable for expansion joint	no
Suitable for screed-flush closed underfloor ducts	no
Suitable for flushfloor, open underfloor trunking	no
Suitable for screed-covered underfloor ducts	no
With screening	no
With connection opening	yes
With equipotential bonding	yes
With separating retainer	no
With overhang	no
Removable cover	yes
ROHS-conformant	yes
Heavy-duty version	no
Separating retainer fastening	rasten
Separating retainer fastening	Lock