


Technical data sheet

Cassette kit for screed installation

Item number: 7429557



Height-adjustable cassette with cord outlet and all the necessary system accessories for the installation in screed floors with dry-cleaned floor covering in indoor areas.

Included in the delivery are:

- Underfloor box UZD350-4R,
- Mounting lid DUG350-3/4,
- Height-adjustment bracket,
- Sticky tape,
- Cassette of nominal size 4 with cord outlet,
- Two universal supports UT3/45 for three Modul 45® devices each. Stainless cassette and cord outlet. Floor covering recess in the cassette: 20 mm.

Master data

Item number	7429557
Type	RKSN2 4 KSD V20
Description 1	Cassette construction set
Description 2	for screed installation
Manufacturer	OBO
Dimension	500x483x167
Smallest sales unit	1
Unit of quantity	Piece
Weight	1220 kg
Weight unit	kg/100 pc.


Technical data sheet

Cassette kit for screed installation



Item number: 7429557

Dimensions



Technical data

Cable outlet version	Swivellable cord outlet
Screed height, max.	160 mm
Screed height, min.	80 mm
ROHS-conformant	Exempt
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK10
Floor covering thickness	20 mm