

Technical data sheet

Underfloor box with GES9UGE

Item number: 7429699



Square screed socket with GES9 UGE service outlet for use in screed floors in indoor areas. With pre-marked insertion openings for pipelines (M25) on all four sides. The delivery includes a cover plate APMT5 blank and a cover plate for 4 data connections of type LUJ6C as well as 1 cover plate APMT5 with double socket switched. The minimum installation depth is 64 mm, the height-adjustment range +23 mm.

The scope of delivery contains three cover plates: A blank version, one switched with a double BS socket and one for the installation of four data connection sockets of type LJ6UC.



PA Polyamide

Master data

Item number	7429699
Type	GES9 BOX 7011 V
Description 1	Service outlet-Set
Description 2	for BS sockets
Manufacturer	OBO
Dimension	264x264x91
Colour	Iron grey; RAL 7011
Material	Polyamide
Smallest sales unit	1
Unit of quantity	Piece
Weight	290 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	12,7726 kg CO2e / 1 Piece


Technical data sheet

Underfloor box with GES9UGE


Item number: 7429699



Dimensions



Length	264 mm
Width	264 mm



Technical data

Number of installable devices	12
Number of mounting boxes	3
Cable outlet version	Swivellable cord outlet
Floor covering protection frame	yes
Floor care	Dry
Seal installation option	no
Screed height, max.	85 mm
Screed height, min.	65 mm
Floor height, max.	95 mm
Floor height, min.	72 mm
Suitable for raised floor installation	no
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	no
Suitable for cavity floor installation	no
Suitable for wet care	no
Suitable for underfloor ducts	no
Device support to accept mounting boxes	yes
Length of external dimensions	264 mm
With floor covering recess	yes
Nominal size for device installation units	9
Height-adjustment range, max.	85 mm
Height-adjustment range, min.	65 mm
Frame version	Carpet protection frame
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK08

Technical data sheet

Underfloor box with GES9UGE

Item number: 7429699



Technical data

Heavy-duty version	no
Installation system type	MT4
Vertical load, large area	to 3,000 N
Vertical load, small area	to 2,000 N
Opening mechanism	Handle
Floor covering thickness	10 mm