

Technical data sheet

Spacer clip ASL 733, black

Item number: 1362870



Spacer clip in black, for the installation of pipes and cables on walls, ceilings and floors. With self-locking cover. Fastening via slot.
Approved for the maintenance of electrical function according to DIN 4102 Part 12, maintenance of electrical function classes E 30 to E 90.



St	Steel
G	Electrogalvanised

Master data

Item number	1362870
Type	ASL 733 17 SW
Description 1	Distance saddle
Description 2	with slot
Manufacturer	OBO
Dimension	14-17mm
Colour	Jet black; RAL 9005
Material	Steel
Surface	Electrogalvanised
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	25
Unit of quantity	Piece
Weight	2.099 kg
Weight unit	kg/100 pc.


Technical data sheet

Spacer clip ASL 733, black

Item number: 1362870



Dimensions



Length	44 mm
Width	14 mm
Height	29 mm

Technical data

Distance to the wall	yes
Number of cables/pipes	1
Version for	Closed
Fastening type	Screw hole
For diameter	14 - 17
Halogen-free	yes
Material thickness	1.5 mm
Clamping range D, max.	17 mm
Clamping range D, min.	14 mm
UV-resistant	yes