

# Technical data sheet

## Pluggable cover, equipped, OBO GST18

Item number: 2006048



Pluggable cover for the closing of junction boxes, equipped with 4 Wieland GST18 plug systems, prewired with lever plug-in connector With quick lock in cover, sealable. Halogen-free material, UV-resistant Flame-resistant to DIN EN 60695/2/11, test temperature 650 °C. Impact resistance IK07 at room temperature. Protection class IP30.



**PP** Polypropylene

### Master data

|                                    |                            |
|------------------------------------|----------------------------|
| Item number                        | 2006048                    |
| Type                               | D01 4x3p WD                |
| Description 1                      | Plug-in cover              |
| Description 2                      | for junction box, equipped |
| Manufacturer                       | OBO                        |
| Dimension                          | 150x116x60                 |
| Colour                             | Light grey; RAL 7035       |
| Material                           | Polypropylene              |
| Smallest sales unit                | 1                          |
| Unit of quantity                   | Piece                      |
| Weight                             | 17.7 kg                    |
| Weight unit                        | kg/100 pc.                 |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,3127 kg CO2e / 1 Piece   |


# Technical data sheet

Pluggable cover, equipped, OBO GST18

Item number: 2006048



## Dimensions



|        |        |
|--------|--------|
| Length | 150 mm |
| Width  | 116 mm |
| Height | 60 mm  |

## Technical data

|                                          |                                                        |
|------------------------------------------|--------------------------------------------------------|
| Number of 3-pole sockets                 | 4                                                      |
| Number of 4-pole sockets                 | 0                                                      |
| Number of 5-pole sockets                 | 0                                                      |
| Version, concealed and cavity wall cover | Suitable for snap-in connector (manufacturer specific) |
| Fastening type                           | Screw fastening                                        |
| Shape                                    | Rectangular                                            |
| Halogen-free                             | yes                                                    |
| ROHS-conformant                          | Exempt                                                 |
| Protection rating                        | IP30                                                   |