

OBO family pack

GEK-K Rapid 45 and GEK-K 80 mm cover

OBO's top models

LFS Cable routing systems



OBO
BETTERMANN

Simply more space


The GEK-K Rapid 45



The GEK-K Rapid 45 device installation trunking can offer a high level of flexibility as the hard PVC trunking allows the mounting of Modul 45 devices without the need for tools. Whether switches, sockets or data technology: the compact design of these devices ensures sufficient installation space in the trunking whilst still appearing attractive. Whether as skirting board trunking for housing or to supply workstations in an office, the Rapid 45 device installation trunking is the perfect solution.


NEW

- Improved material recipe
- VDE-tested
- Lead-free
- Stable profile quality thanks to optimum wall thickness
- Standard range of colours
- Cover clip with multiple uses
- Flexible floor perforation for ease of mounting
- Fittings for all applications
- Partition wall installation for different voltage levels
- Large product range for device installation including time-saving Modul 45 technology
- Intelligent logistics solution



GEK-K Device installation trunking
Plastic systems
Rapid 45

GEK-K Device installation trunking
Plastic systems
80 mm cover
Order the cover separately



Type	GEK-K 53100	GEK-K 53160	GEK-K 53160-3	GEK-K 70110	GEK-K 70135	GEK-K 70170	GEK-OT 80
Packing unit in m	8	8	8	8	8	8	16
Pure white Similar to RAL 9010	6116 02 7	6116 05 1	6116 07 3	6270 11 5	6270 19 0	6270 26 3	6270 81 6
Cream Similar to RAL 9001	-	-	-	6270 10 7	6270 18 2	6270 25 5	6270 80 8
Light grey Similar to RAL 7035	-	-	-	6270 13 1	6270 21 2	6270 29 8	6270 83 2
Stone grey Similar to RAL 7030	-	-	-	6270 12 3	6270 20 4	6270 27 1	6270 82 4
Accessories	✓	✓	✓	✓	✓	✓	-
Fittings	✓	✓	✓	✓	✓	✓	-
Device installation	-	-	-	✓	✓	✓	-
Device installation Modul 45	✓	✓	✓	✓	✓	✓	-

Always on the right track

The GEK-K 80 mm cover



This device installation trunking can be equipped not just with conventional switch and plug-in devices, but, using an adapter, also with the devices of the Modul 45 system. All the device installation trunking of this series has a cover width of 80 mm. The generous dimensions provide sufficient space for device installation and cable routing.

Accessories

GEK-K Rapid 45:

- Bend radius for standardised installation of data cables and fibre-optic cables.

GEK-K 80 mm cover:

- Complete range of accessories such as adapters for accepting Modul 45 devices, fixing panels, convection grids, noise reduction and everything else required for installation.
- Installation accessories for 16 A CEE sockets.
- Bend radius for perfect installation of data cables and fibre-optic cables.

Fittings

GEK-K Rapid 45:

- Complete product range with all required fittings such as joint cover, internal corner, external corner, flat angle, end and T-pieces. The joint cover also covers the cut edges of the trunking.
- Variable fittings (adjustable between 70° and 130°) for perfect installation for non right-angled corners.

GEK-K 80 mm cover:

- Complete product range with all required fittings such as internal corner, external corner, flat angle, end and T-piece, partition and wall covers.

Device installation

GEK-K Rapid 45:

- For direct installation of switch and plug-in Modul 45 devices.
- Complete range of Modul 45 switch and plug-in devices: switches, power sockets, data network technology, telecommunications, TV, etc.

GEK-K 80 mm cover:

- Fittable both with standard switch and plug-in devices of all manufacturers and with the quick to install, space-saving Modul 45 technology.
- Special accessory mounting box with winding aid for the installation of fibre-optic data boxes.



Good prospects: clear design and high material quality

Classically reduced, with straight lines and clear shapes: the LFS cable routing trunking systems are the perfect choice for modern installation concepts, whether at home, in the office or in the factory. The trunking is made of high-quality, low flammability hard PVC. The perfect PVC mixture ensures easy handling during installation, maximum carrying and holding properties on the wall and a long life. All the trunking is VDE-certified and fulfils the standards DIN EN 50085-2-1 (WDK) and DIN EN 50085-2-2 (GEK-K Rapid/GEK-K 80 mm cover).

Besides this plastic trunking, OBO offers a comprehensive range of sheet steel and aluminium trunking and service pole systems. It can fulfil any requirements for functionality and design.



© OBO BETTERMANN Order no. 9136629 05/2008 EN

OBO BETTERMANN GmbH & Co. KG
P.O. Box 1120 · 58694 Menden · Germany
Tel. +49 (0)2373/89-0 · Fax +49 (0)2373/89-238
E-mail: info@obo.de · www.obo.de

Central Technical Hotline
Telephone +49 (0)2373/89-1500
Fax +49 (0)2373/89-1550
E-mail hotline@obo.de

OBO
BETTERMANN