Technical data sheet

Clamp clip 2056 N foot, single, for screen connection, metal pressure sleeve, VA
Item number: 1167070

Clamp clip with N foot, metal pressure sleeve with rounded edges to protect the cable. For electrical connection of braiding on screened cables. For vertical and horizontal mounting of 1 single cable on a C-profile rail. For slot width 11–12 mm. With 1-start screw thread on pressure sleeve, universal hexagonal screw head WAF10, with slot and cross recess. Suitable for mounting indoors and outdoors. The cable screen can also be used for equipotential bonding if both ends are connected to the reference potential. Counter-trough contained in scope of delivery.

11-12 N

A2 Stainless steel

2B Bright, treated

Master data

Item number	1167070
Type	BS-SAS-M-28 A2
Description 1	Clamp clip 2056
Description 2	for shield attachment
Manufacturer	OBO
Dimension	22-28
Material	Stainless steel 1.4301
Surface Surface standard	Bright, treated
Smallest sales unit	50
Unit of quantity	Piece
Weight	6.206 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,4524 kg CO2e / 1 Piece

Technical data sheet

Clamp clip 2056 N foot, single, for screen connection, metal pressure sleeve, VA
Item number: 1167070

Dimensions

Length	22.5 mm
Width	33 mm
Height	52 mm
Plate thickness	2 mm
Dimension A	22.5 mm
Dimension B	33 mm
Dimension C	35 mm
Dimension G (mm)	M6
Dimension H	52 mm
Dimension L	34 mm
Dimension t	1.5 mm

Technical data

Number of cables/pipes	1
For pipe diameter, max.	28 mm
For pipe diameter, min.	22 mm
for rail with slot width (with interval), max.	12 mm
for rail with slot width (with interval), min.	11 mm
Thread	M6
Halogen-free	yes
Length of external dimensions	35 mm
Max. Tightening torque	3 Nm
With metal trough	yes
Mounting type	Profile rail
Slot width	10 mm
Clamping range D, max.	28 mm
Clamping range D, min.	22 mm
Surface addition	Untreated
Material addition	Rustproof steel
With counter-trough	yes
Material of trough	Rustproof steel
Material quality of trough	Stainless steel 304 (1.4301)
Material of counter-trough	Rustproof steel