# Technical data sheet

## Flat cable threaded connection, metric thread M25, stone grey

## Item number: 2013013

Flat-cable entry, choke-nipple design with metric connecting thread to IEC 432, protection rating IP31, with pre-mounted support sealing ring 107/F.

650° HALOGEN FREE CE UKCA IP 31 M

PE Polyethylene

### Master data

| | |
|---|---|
| Item number | 2013013 |
| Type | 106 FL M25 14 40 |
| Description 1 | Flat cable threaded connection |
| Manufacturer | OBO |
| Dimension | M25 |
| Colour | Stone grey; RAL 7030 |
| Material | Polyethylene |
| Smallest sales unit | 25 |
| Unit of quantity | Piece |
| Weight | 2.68 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,0812 kg CO2e / 1 Piece |

# Technical data sheet

## Flat cable threaded connection, metric thread M25, stone grey

## Item number: 2013013

### Dimensions







| | |
|---|---|
| Dimension A | 30 mm |
| Dimension B | 56 mm |
| Dimension D | 35 mm |
| Dimension G | M25 mm |
| Dimension L | 52 mm |
| Dimension L1 | 12 mm |
| Dimension L2 | 40 mm |

### Technical data

| | |
|---|---|
| Type of seal | Sealing ring |
| Version for | Straight |
| Bend protection | yes |
| explosion-proof | no |
| Flat cable/width, max. | 40 mm |
| Flat cable/width, min. | 37 mm |
| Flat cables/thickness, max. | 14 mm |
| Flat cables/thickness, min. | 11 mm |
| Flat cable gland | yes |
| For Ex zone | Without |
| Thread | M25 |
| Thread type | Metric |
| Fibre-glass reinforced | no |
| Sealing insert, multiple | no |
| With locknut | no |
| ROHS-conformant | yes |
| Impact-resistant | no |
| Protection rating | IP31 |
| Strain relief option | no |