# Technical data sheet

## Expansion piece, metric thread

## Item number: 2088286

Extension made from brass with metric inner and outer thread to mount metal or plastic cable glands on housings. IP54 protection rating without additional connection sleeve. Protection rating of up to IP68 possible with additional connection seal, such as an O-ring or flat sealing ring.

CE M

CuZn 37 Brass

N Nickel-plated

### Master data

| | |
|---|---|
| Item number | 2088286 |
| Type | 165 ADA M 50-63 |
| Description 1 | Extension |
| Description 2 | M - M |
| Manufacturer | OBO |
| Dimension | M50-M63 |
| Material | Brass |
| Surface<br>Surface standard | Nickel-plated |
| Smallest sales unit | 5 |
| Unit of quantity | Piece |
| Weight | 13.06 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,3913 kg CO2e / 1 Piece |

# Technical data sheet

## Expansion piece, metric thread

## Item number: 2088286

### Dimensions

| | |
|---|---|
| Dimension D | 43.4 mm |
| Dimension E | 69.9 mm |
| Dimension G1 (mm) | 50 |
| Dimension G2 (mm) | 63 |
| Dimension L | 33 mm |
| Dimension L1 | 9.2 mm |
| Dimension L2 | 16 mm |
| Dimension L4 | 7 mm |




### Technical data

| | |
|---|---|
| explosion-proof | no |
| Thread type: External thread | Metric |
| Thread type: Internal thread | Metric |
| Thread dimension, metric, external | 50 |
| Thread dimension, metric, internal | 63 |
| ROHS-conformant | Exempt |
| WAF | 65 |
| Nickel-plated | yes |