Technical data sheet

Bolt tie FAZ II P G

Item number: 3498902

Bolt tie FAZ II Plus for the anchoring of medium to heavy loads in cracked or uncracked concrete. Suitable for high loads with small edge and axial distances. For knocking in.
European Technical Assessment ETA-99/0520, including characteristic values under fire exposure to fire resistance R 120.
Proof of suitability in the event of seismic impacts, categories C1 and C2.

CE

St	Steel
G	Electrogalvanised

Master data

Item number	3498902
Type	FAZIIPlus 8/30
Description 1	Bolt anchor
Description 2	with large washer
Manufacturer	OBO
Dimension	M8x95
Colour	zinc
Material	Steel
Surface	Electrogalvanised
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	50
Unit of quantity	Piece
Weight	4.3 kg
Weight unit	kg/100 pc.

Dimensions



Length	95 mm
Dimension L	95 mm

Technical data sheet

Bolt tie FAZ II P G

Item number: 3498902

Technical data

Version for	For pushing in
Anchor/nail/bolt version	Spreading anchor
Drill hole depth	57.5 mm
Drill hole diameter, min.	8 mm
Thread	M8
Thread metric	8
Thread type	Metric
Thread length	58 mm
Clamping strength	30 mm
ROHS-conformant	yes
WAF	13
Approvals available	yes
Mounting type, anchor, tie	Push-through mounting Pre-mounting Stand-off mounting
Tie screw system	Hexagon head
Clamping range, max.	40 mm
Clamping range, min.	30 mm
ETA earthquake rating	C1