Technical data sheet

Bolt tie FAZ II P G

Item number: 3498906

Bolt tie FAZ II Plus for the anchoring of medium to heavy loads in cracked or uncracked concrete. Suitable for high loads with small edge and axial distances. For knocking in.
European Technical Assessment ETA-99/0520, including characteristic values under fire exposure to fire resistance R 120.
Proof of suitability in the event of seismic impacts, categories C1 and C2.

CE

St	Steel
G	Electrogalvanised

Master data

Item number	3498906
Type	FAZIIPlus 8/100
Description 1	Bolt anchor
Description 2	with large washer
Manufacturer	OBO
Dimension	M8x165
Colour	zinc
Material	Steel
Surface	Electrogalvanised
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	25
Unit of quantity	Piece
Weight	5.7 kg
Weight unit	kg/100 pc.

Dimensions

Length	165 mm
Dimension L	165 mm

Technical data sheet

Bolt tie FAZ II P G

Item number: 3498906

Technical data

Version for	For pushing in
Anchor/nail/bolt version	Spreading anchor
Drill hole depth	57.5 mm
Drill hole diameter, min.	8 mm
Thread	M8
Thread metric	8
Thread type	Metric
Thread length	128 mm
Clamping strength	100 mm
ROHS-conformant	yes
WAF	13
Approvals available	yes
Mounting type, anchor, tie	Push-through mounting Pre-mounting Stand-off mounting
Tie screw system	Hexagon head
Clamping range, max.	110 mm
Clamping range, min.	100 mm
ETA earthquake rating	C1