Technical data sheet

Bolt tie FAZ II P G

Item number: 3498938

Bolt tie FAZ II Plus for the anchoring of medium to heavy loads in cracked or uncracked concrete. Suitable for high loads with small edge and axial distances. For knocking in.
European Technical Assessment ETA-99/0520, including characteristic values under fire exposure to fire resistance R 120.
Proof of suitability in the event of seismic impacts, categories C1 and C2.

CE

St	Steel
G	Electrogalvanised

Master data

Item number	3498938
Type	FAZIIPlus 12/100
Description 1	Bolt anchor
Manufacturer	OBO
Dimension	M12x200
Colour	zinc
Material	Steel
Surface	Electrogalvanised
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	20
Unit of quantity	Piece
Weight	17.4 kg
Weight unit	kg/100 pc.

Dimensions



Length	200 mm
Dimension L	200 mm

Technical data sheet

Bolt tie FAZ II P G

Item number: 3498938

Technical data

Version for	For pushing in
Anchor/nail/bolt version	Spreading anchor
Drill hole depth	88.5 mm
Drill hole diameter, min.	12 mm
Thread	M12
Thread metric	12
Thread type	Metric
Thread length	151 mm
Clamping strength	100 mm
ROHS-conformant	yes
WAF	19
Approvals available	yes
Mounting type, anchor, tie	Push-through mounting Pre-mounting Stand-off mounting
Tie screw system	Hexagon head
Clamping range, max.	120 mm
Clamping range, min.	100 mm
ETA earthquake rating	C1 and C2