Technical data sheet

Mesh cable tray connector, long A4

Item number: 6016688

Long mesh cable tray connection for screwless straight connection of mesh cable trays.
Two straight connectors, type GRV 245, are used for each connection point.

Can be used from a mesh cable tray width of 100 mm.

The FS variant is used to connect electrogalvanised mesh cable trays, the DD variant to connect hot/hot-dip galvanised mesh cable trays and the VA variant to connect stainless steel mesh cable trays.

A4 Stainless steel

2B Bright, treated

Master data

Item number	6016688
Type	GRV 245 A4
Description 1	Quick connector
Description 2	for mesh cable tray, long type
Manufacturer	OBO
Dimension	L245mm
Colour	stainless steel
Material	Stainless steel 1.4404
Surface	Bright, treated
Surface standard	
Smallest sales unit	20
Unit of quantity	Piece
Weight	13.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,8642 kg CO2e / 1 Piece

Technical data sheet

Mesh cable tray connector, long A4

Item number: 6016688

Dimensions



Dimension	245 x 30
Length	245 mm
Width	30 mm
Width	1.18 in
Height	14 mm
Height	0.55 in
Plate thickness	2 mm

Technical data

Version for	Straight connector
Maintain electrical functions	no
Suitable for mesh cable tray	yes
Suitable for cable ladder	no
Suitable for cable tray	no
Adjustable connector, horizontal	no
Articulated connector, vertical	no
ROHS-conformant	yes
Rustproof steel, pickled	no
Connection type	Screwless connector