# Technical data sheet

## Trunking, type WDK 60110

## Item number: 6027121

Trunking cover and base with base perforation.
Four cover fixing devices included.
Lid clamp can be moved along the entire length of the trunking.

PVC Polyvinylchloride

### Master data

| | |
|---|---|
| Item number | 6027121 |
| Type | WDK60110LGR |
| Description 1 | Wall trunking system |
| Description 2 | with base perforation |
| Manufacturer | OBO |
| Dimension | 60x110x2000 |
| Colour | Light grey; RAL 7035 |
| Material | Polyvinylchloride |
| Smallest sales unit | 16 |
| Unit of quantity | Metre |
| Weight | 117 kg |
| Weight unit | kg/100 m |
| CO2 Footprint (GWP) Cradle-to-Gate | 2,3554 kg CO2e / 1 Meter |

# Technical data sheet

## Trunking, type WDK 60110

## Item number: 6027121

### Dimensions




| | |
|---|---|
| Length | 2,000 mm |
| Width | 108.5 mm |
| Height | 60.3 mm |

### Technical data

| | |
|---|---|
| Number of fixed partitions | 0 |
| Number of cables NYM 3 x 1.5 mm² Ø 10.5 mm (without socket) | 29 |
| Number of cables NYM 3 x 2.5 mm² Ø 11.5 mm (without socket) | 24 |
| Number of cables NYM 5 x 1.5 mm² Ø 12.0 mm (without socket) | 22 |
| Number of insertable partitions | 1 |
| Version, cable trunking cover | Loose |
| Fastening type | Base perforation |
| Maintain electrical functions | no |
| Halogen-free | no |
| Cable retaining clip | yes |
| Duct connector | no |
| Delivery on a roll | no |
| Usable cross-section | 5076 mm² |
| ROHS-conformant | yes |
| Protective film | no |
| Protection rating IK code | IK04 |
| Permitted temperature range, max. | 60 °C |
| Permitted temperature range, min. | -5 °C |