Technical data sheet

Trunking, type WDK 25025S with adhesive film

Item number: 6027372

Wall and ceiling trunking with base perforation and adhesive film consisting of cover and base for mounting directly on the wall.

PVC Polyvinylchloride

Master data

Item number	6027372
Type	WDK25025SRW
Description 1	Wall trunking system
Description 2	with adhesive film
Manufacturer	OBO
Dimension	25x25x2000
Colour	Pure white; RAL 9010
Material	Polyvinylchloride
Smallest sales unit	30
Unit of quantity	Metre
Weight	18.4 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	0,8304 kg CO2e / 1 Meter

Technical data sheet

Trunking, type WDK 25025S with adhesive film

Item number: 6027372

Dimensions



Length	2,000 mm
Width	25 mm
Height	25 mm

Technical data

Number of fixed partitions	0
Number of cables NYM 3 x 1.5 mm² Ø 10.5 mm (without socket)	2
Number of cables NYM 3 x 2.5 mm² Ø 11.5 mm (without socket)	2
Number of cables NYM 5 x 1.5 mm² Ø 12.0 mm (without socket)	2
Number of insertable partitions	0
Version, cable trunking cover	Loose
Fastening type	Base perforation
Maintain electrical functions	no
Halogen-free	no
Cable retaining clip	no
Duct connector	no
Delivery on a roll	no
Usable cross-section	460 mm²
ROHS-conformant	yes
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C