Technical data sheet

Cable tray, marine standard A2

Item number: 6045840

Cable tray for use in ship construction, produced according to the marine standard VG 88900-1.



A2	Stainless steel
2B	Bright, treated

Master data

Item number	6045840
Type	MKR 15 200 A2
Description 1	Cable tray marine standard
Description 2	Material thickness 1.50mm
Manufacturer	OBO
Dimension	15x200x2000
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	2
Unit of quantity	Metre
Weight	194.7 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	17,6094 kg CO2e / 1 Meter

Technical data sheet

Cable tray, marine standard A2

Item number: 6045840

Dimensions



Dimension	15 X 200
Length	2,000 mm
Width	200 mm
Height	15 mm
Plate thickness	1.5 mm
Dimension B	200 mm

Technical data

Connector version	Without connectors
Walkable	no
Maintain electrical functions	no
With cover	no
Mounting perforation in base	yes
NATO hole pattern	yes
ROHS-conformant	yes
Rustproof steel, pickled	yes
Side perforation	no
Wide-span version	no
Load test type according to IEC 61537	Type II
Type of connector, cable support system	Screwed

Loads

Support spacing 1.0 m	0.75 kN/m
Support spacing 1.5 m	0.25 kN/m