Technical data sheet

Cover for stand-off mounting A2

Item number: 6051194

Cover for stand-off mounting. Not suitable for the vertical ladders SLM and SLS. Spacers must be ordered separately for every 3 m under article number 6065475 for cable trays and cable ladders as well as under article number 6065477 for wide span systems.
When using covers outdoors, additional measures against the influence of wind must be taken.

A2	Stainless steel
2B	Bright, treated

Master data

Item number	6051194
Type	DRL FAM 330 A2
Description 1	Cover for offset mounting
Description 2	without spacer bracket
Manufacturer	OBO
Dimension	330x3000
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	3
Unit of quantity	Metre
Weight	417.14 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	21,134 kg CO2e / 1 Meter

Technical data sheet

Cover for stand-off mounting A2

Item number: 6051194

Dimensions



Length	3,000 mm
Width	330 mm
Plate thickness	1.5 mm

Technical data

Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	yes
ROHS-conformant	yes
Rustproof steel, pickled	no