Technical data sheet

45° fitting, right, BKRS 100 FS

Item number: 6061904

Cable tray fitting with 45° cut, for creation of bends on walkable cable trays.

CE

St	Steel
FS	Strip galvanised

Master data

Item number	6061904
Type	BKRS 1020 45R FS
Description 1	Cable tray BKRS
Description 2	mitre right side
Manufacturer	OBO
Dimension	100x200x1000
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	552 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	17,7505 kg CO2e / 1 Piece

Technical data sheet

45° fitting, right, BKRS 100 FS

Item number: 6061904

Dimensions



Length	1,000 mm
Width	200 mm
Height	100 mm
Plate thickness	2 mm
Dimension B	200 mm
Dimension H	100 mm
Dimension L	1,000 mm

Technical data

Bend (angle)	45°
Connector version	Without connectors
Type	Bend, rigid
Walkable	yes
Maintain electrical functions	no
Mounting perforation in base	yes
NATO hole pattern	no
Change of direction	Horizontal
ROHS-conformant	yes
Rustproof steel, pickled	no
Side perforation	yes
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C
Wide-span version	no
Type of connector, cable support system	Screwed