# Technical data sheet

## BKRS 100 cable tray, shortened FS

## Item number: 6061970

Cable tray fitting with shortened length, for creation the of straight sections on walkable cable trays.

CE

| | |
|---|---|
| St | Steel |
| FS | Strip galvanised |

### Master data

| | |
|---|---|
| Item number | 6061970 |
| Type | BKRS 1010 15 FS |
| Description 1 | Cable tray BKRS |
| Description 2 | walkable |
| Manufacturer | OBO |
| Dimension | 100x100x1500 |
| Colour | zinc |
| Material | Steel |
| Surface | Strip galvanised |
| Surface standard | DIN EN 10346 |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 723.9 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 19,7511 kg CO2e / 1 Piece |

# Technical data sheet

## BKRS 100 cable tray, shortened FS

## Item number: 6061970

### Dimensions




| | |
|---|---|
| Length | 1,500 mm |
| Width | 100 mm |
| Height | 100 mm |
| Plate thickness | 2 mm |
| Dimension B | 100 mm |
| Dimension H | 100 mm |

### Technical data

| | |
|---|---|
| Connector version | Without connectors |
| Mounting system fastening type | Floor |
| Walkable | yes |
| Maintain electrical functions | no |
| With cover | no |
| Mounting perforation in base | yes |
| NATO hole pattern | no |
| Usable cross-section | 96 cm² |
| Usable cross-section | 9600 mm² |
| ROHS-conformant | yes |
| Rustproof steel, pickled | no |
| Side perforation | no |
| Wide-span version | no |
| Type of connector, cable support system | Screwed |