# Technical data sheet

## VGA connection, 1 module, straight outlet, as screw connection
## Item number: 6104613

Multimedia support with one VGA connection socket, straight cable outlet, with labelling panel, VGA socket (HD15) with screw connection. Support plate with locking fastening, suitable for horizontal and vertical installation in the system environment.

PC Polycarbonate

### Master data

| | |
|---|---|
| Item number | 6104613 |
| Type | MTG-VGA S SWGR1 |
| Description 1 | Multimedia support, VGA |
| Description 2 | socket with screw connection |
| Manufacturer | OBO |
| Dimension | 45x45mm |
| Colour | Black-grey; RAL 7021 |
| Material | Polycarbonate |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 2.4 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,0737 kg CO2e / 1 Piece |

# Technical data sheet

## VGA connection, 1 module, straight outlet, as screw connection
## Item number: 6104613

### Dimensions







| | |
|---|---|
| Width | 45 mm |
| Height | 45 mm |

### Technical data

| | |
|---|---|
| Surface version | Matt |
| Fastening type | Lock |
| Labelling panel | With labelling panel |
| Halogen-free | yes |
| Hinged cover | no |
| Lamp-wire connector | no |
| With printed label | no |
| With dust protection | no |
| ROHS-conformant | yes |
| Protection rating | IP20 |
| Depth | 9 mm |
| Support ring | no |
| Transparent | no |
| Use | VGA |
| Strain relief option | no |
| Combination | Basic element with central cover plate |
| Outlet direction | Straight |