# Technical data sheet

## BNC connection, 1 module, slanting outlet, as 1:1 coupling, black-grey
## Item number: 6105033

Multimedia support with one BNC connection socket, slanting cable outlet, with labelling panel, BNC cinch coupling, socket-socket version. Support plate with locking fastening, suitable for horizontal and vertical installation in the system environment.

PC Polycarbonate

### Master data

| | |
|---|---|
| Item number | 6105033 |
| Type | MTS-BC F SWGR1 |
| Description 1 | Multimedia support, video BNC |
| Description 2 | 1x coupling, socket-socket |
| Manufacturer | OBO |
| Dimension | 45x45mm |
| Colour | Black-grey; RAL 7021 |
| Material | Polycarbonate |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 1.7 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,1649 kg CO2e / 1 Piece |

# Technical data sheet

## BNC connection, 1 module, slanting outlet, as 1:1 coupling, black-grey
## Item number: 6105033

### Dimensions




| | |
|---|---|
| Width | 45 mm |
| Height | 45 mm |

### Technical data

| | |
|---|---|
| Number of units | 1 |
| Surface version | Matt |
| Fastening type | Lock |
| Halogen-free | yes |
| Hinged cover | no |
| Lamp-wire connector | no |
| With printed label | no |
| With dust protection | no |
| ROHS-conformant | Exempt |
| Protection rating | IP20 |
| Depth | 26 mm |
| Support ring | no |
| Transparent | no |
| Use | BNC/TNC |
| Strain relief option | no |
| Combination | Basic element with central cover plate |
| Outlet direction | Sloping |