Technical data sheet

XLR connection, 1 module, straight outlet, 3-pin connector, as soldered connection, aluminium-painted
Item number: 6105228

Multimedia support with one XLR connection socket, straight cable outlet, without labelling panel, 3-pin XLR connector with soldered connection. Support plate with locking fastening, suitable for horizontal and vertical installation in the system environment.

PC Polycarbonate

Master data

Item number	6105228
Type	MTG-X3M L AL1
Description 1	Multimedia support, XLR, 3-pin
Description 2	connector w. sold. connection
Manufacturer	OBO
Dimension	45x45mm
Colour	Aluminium painted
Material	Polycarbonate
Smallest sales unit	1
Unit of quantity	Piece
Weight	3 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0394 kg CO2e / 1 Piece

Technical data sheet

XLR connection, 1 module, straight outlet, 3-pin connector, as soldered connection, aluminium-painted
Item number: 6105228

Dimensions





Width	45 mm
Height	45 mm

Technical data

Surface version	Matt
Fastening type	Lock
Labelling panel	With labelling panel
Halogen-free	yes
Hinged cover	no
Lamp-wire connector	no
With printed label	no
With dust protection	no
ROHS-conformant	Exempt
Protection rating	IP20
Depth	9 mm
Support ring	no
Transparent	no
Use	XLR
Strain relief option	no
Combination	Basic element with central cover plate