Technical data sheet

3-wire connection cable, halogen-free, cross-section 2.5 mm², 1 m length, white
Item number: 6108732



Connection cable 3 x 2.5 mm² in the version socket-connector, type WINSTA® MIDI.

Hose pipe: H05Z1Z1-F 3 x 2.5 mm²
Suitable for connection of ready-for-connection universal supports Connect UTC to an energy distributor.

CE

PA Polyamide

Master data

Item number	6108732
Type	VL-WIN 3P2.5H1W
Description 1	Connection cable
Description 2	3x2,5mm², WINSTA
Manufacturer	OBO
Dimension	1000x27x15
Colour	White
Material	Polyamide
Smallest sales unit	1
Unit of quantity	Piece
Weight	16.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,6582 kg CO2e / 1 Piece

Dimensions

Technical data sheet

3-wire connection cable, halogen-free, cross-section 2.5 mm², 1 m length, white
Item number: 6108732

Technical data

Number of poles	3
Type of terminated cable	Connection cable
Type of locking	Separate
Version, page 1	socket
Version, page 2	Connector
Rated surge voltage	4
Fire load	0.88
Colour of the coding/contact insert	White
Halogen-free	yes
Cable type	H05Z1Z1-F
Cable length	1000 mm
Jacket colour	White
Nominal voltage	250 V
Nominal current	20 A
Pin labelling	L, N, PE
Cross-section	1.5 mm²
ROHS-conformant	yes
Protection rating	IP20
Degree of soiling	3