# Technical data sheet

## Trunking connector and joint cover

## Item number: 6113214

Joint cover for the bases of the Rapid 45 device installation trunking to hide cut edges and provide a perfect connection of the trunking segments. The joint covers are attached. Suitable for trunking width 130 mm.

PC/ABS Polycarbonate/Acrylnitrile-butadiene-styrene

### Master data

| | |
|---|---|
| Item number | 6113214 |
| Type | GK-KS45-2AL |
| Description 1 | Joint cover |
| Description 2 | for Rapid 45-2 130 |
| Manufacturer | OBO |
| Dimension | 133x55x15 |
| Colour | aluminium |
| Material | Polycarbonate/Acrylnitrile-butadiene-styrene |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 0.45 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,1003 kg CO2e / 1 Piece |

# Technical data sheet

## Trunking connector and joint cover

## Item number: 6113214

### Dimensions




| | |
|---|---|
| Length | 15 mm |
| Width | 55 mm |
| Height | 17 mm |

### Technical data

| | |
|---|---|
| Version for | Trunking cut cover |
| Fastening type | Slide (before mounting) |
| Shape | Symmetrical |
| for duct width | 130 mm |
| for trunking height | 53 mm |
| Halogen-free | yes |
| Cover width | 45 mm |
| ROHS-conformant | yes |
| Protection rating | IP40 |
| Protection rating IK code | IK08 |
| Permitted temperature range, max. | 60 °C |
| Permitted temperature range, min. | -15 °C |