# Technical data sheet

## Device installation trunking Rapid 45-2, trunking width 165, trunking height 53
## Item number: 6113402



Trunking base and cover with base perforation for direct wall mounting.

PVC Polyvinylchloride

### Master data

| | |
|---|---|
| Item number | 6113402 |
| Type | GK-53165LGR |
| Description 1 | Device installation trunking |
| Description 2 | Rapid 45-2, 2-compartment |
| Manufacturer | OBO |
| Dimension | 53x165x2000 |
| Colour | Light grey; RAL 7035 |
| Material | Polyvinylchloride |
| Smallest sales unit | 2 |
| Unit of quantity | Metre |
| Weight | 216.25 kg |
| Weight unit | kg/100 m |
| CO2 Footprint (GWP) Cradle-to-Gate | 4,3824 kg CO2e / 1 Meter |

# Technical data sheet

## Device installation trunking Rapid 45-2, trunking width 165, trunking height 53
## Item number: 6113402

### Dimensions




| | |
|---|---|
| Length | 2,000 mm |
| Width | 165 mm |
| Height | 53 mm |

### Technical data

| | |
|---|---|
| Number of covers | 2 |
| Number of insertable partitions | 2 |
| Rear panel version (inner side) | Continuous C profile |
| Rectangular shape | yes |
| Base perforation | With base perforation |
| Halogen-free | no |
| Cable retaining clip | no |
| Duct connector | no |
| Cover mounting type | Internal |
| Mounting perforation in base | yes |
| Usable cross-section | 7000 mm² |
| Cover supplied | yes |
| Cover width | 45 mm |
| Cover width 2 | 45 mm |
| Cover width 3 | 0 mm |
| Protection rating | IP40 |
| Protective film | yes |
| Protection rating IK code | IK08 |
| Symmetrical | yes |
| Permitted temperature range, max. | 60 °C |
| Permitted temperature range, min. | -15 °C |