# Technical data sheet

## Trunking, type WDKH 30045

## Item number: 6175405

Trunking cover and base with base perforation made of halogen-free plastic. During installation, ensure that only halogen-free accessories and fastening materials are used.

HALOGEN FREE

PC/ ABS Polycarbonate/Acrylnitrile-butadiene-styrene

### Master data

| | |
|---|---|
| Item number | 6175405 |
| Type | WDKH-30045RW |
| Description 1 | Wall trunking system |
| Description 2 | halogen-free |
| Manufacturer | OBO |
| Dimension | 30x45x2000 |
| Colour | Pure white; RAL 9010 |
| Material | Polycarbonate/Acrylnitrile-butadiene-styrene |
| Smallest sales unit | 48 |
| Unit of quantity | Metre |
| Weight | 24.9 kg |
| Weight unit | kg/100 m |
| CO2 Footprint (GWP) Cradle-to-Gate | 1,5036 kg CO2e / 1 Meter |

# Technical data sheet

## Trunking, type WDKH 30045

## Item number: 6175405

### Dimensions




| | |
|---|---|
| Length | 2,000 mm |
| Width | 45 mm |
| Height | 30 mm |

### Technical data

| | |
|---|---|
| Number of fixed partitions | 0 |
| Number of cables NYM 3 x 1.5 mm² Ø 10.5 mm (without socket) | 5 |
| Number of insertable partitions | 0 |
| Version, cable trunking cover | Loose |
| Fastening type | Base perforation |
| Base perforation | with base perforation |
| Maintain electrical functions | no |
| Halogen-free | yes |
| Cable retaining clip | no |
| Duct connector | no |
| Delivery on a roll | no |
| Usable cross-section | 1145 mm² |
| ROHS-conformant | yes |
| Protection rating | IP30 |
| Protective film | no |
| Protection rating IK code | IK07. |
| Permitted temperature range, max. | 90 °C |
| Permitted temperature range, min. | -5 °C |