# Technical data sheet

## Trunking, type WDK 60170

## Item number: 6191258

Trunking cover and base with base perforation.
Four cover clips included.
Lid clamp can be moved along the entire length of the trunking.

PVC Polyvinylchloride

### Master data

| | |
|---|---|
| Item number | 6191258 |
| Type | WDK60170RW |
| Description 1 | Wall trunking system |
| Description 2 | with base perforation |
| Manufacturer | OBO |
| Dimension | 60x170x2000 |
| Colour | Pure white; RAL 9010 |
| Material | Polyvinylchloride |
| Smallest sales unit | 8 |
| Unit of quantity | Metre |
| Weight | 178 kg |
| Weight unit | kg/100 m |
| CO2 Footprint (GWP) Cradle-to-Gate | 3,7671 kg CO2e / 1 Meter |

# Technical data sheet

## Trunking, type WDK 60170

## Item number: 6191258

### Dimensions




| | |
|---|---|
| Length | 2,000 mm |
| Width | 170 mm |
| Height | 60 mm |

# Technical data sheet

## Trunking, type WDK 60170

## Item number: 6191258

### Technical data

| | |
|---|---|
| Number of fixed partitions | 0 |
| Number of cables NYM 3 x 1.5 mm² Ø 10.5 mm (without socket) | 46 |
| Number of cables NYM 3 x 2.5 mm² Ø 11.5 mm (without socket) | 39 |
| Number of cables NYM 5 x 1.5 mm² Ø 12.0 mm (without socket) | 35 |
| Number of insertable partitions | 2 |
| Version, cable trunking cover | Loose |
| Fastening type | Base perforation |
| Halogen-free | no |
| Cable retaining clip | yes |
| Duct connector | no |
| Delivery on a roll | no |
| Usable cross-section | 8089 mm² |
| ROHS-conformant | yes |
| Protection rating | IP30 |
| Protective film | no |
| Protection rating IK code | IK04 |
| Permitted temperature range, max. | 60 °C |
| Permitted temperature range, min. | -5 °C |
| Weatherproof | yes |