Technical data sheet

Straight connector wide spann system 160 FT SOMY

Item number: 6227732



Straight connector for straight connections of cable trays, wide span cable trays and ladders with a side height of 160 mm.
Including appropriate bolts, washers and nuts.

St Steel

FT SO Hot-dip galvanised 85 µm

Master data

Item number	6227732
Type	WRVL 160 FT SO
Description 1	Straight connector
Description 2	for wide span system 160
Manufacturer	OBO
Dimension	160x500
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised 85 µm
Surface standard	DIN EN ISO 1461
Smallest sales unit	2
Unit of quantity	Piece
Weight	221 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	5,4288 kg CO2e / 1 Piece

Technical data sheet

Straight connector wide spann system 160 FT SOMY

Item number: 6227732

Dimensions



Length	500 mm
Width	20 mm
Height	160 mm
Plate thickness	2.5 mm

Technical data

Version for	Straight connector
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	yes
Suitable for cable tray system height	160 mm
Adjustable connector, horizontal	no
Articulated connector, vertical	no
ROHS-conformant	yes
Rustproof steel, pickled	no
Connection type	Screw connector