Technical data sheet

Device installation trunking Rapid 80, trunking width 170, trunking height 90, asymmetrical
Item number: 6279503

Device installation trunking Without base perforation for direct wall mounting or mounting on panels. Over-lengths up to 6,000 mm for trunking bases and covers as well as other RAL colours can be provided on request. The visible surfaces of the painted device installation trunking are laminated.
The cover must be ordered separately. We recommend the use of the duct clamp.
Note:
For anodised device installation trunking and fittings made from aluminium, light colour differences caused by tolerance based on the material and process conditions, cannot be avoided (according to DIN 17 611). Alternatively, we recommend powder coating in the colour RAL 9006 (white aluminium).

Alu Aluminium

EL Anodised

Master data

Item number	6279503
Type	GA-A90170EL
Description 1	Device installation trunking
Description 2	asymmetrical
Manufacturer	OBO
Dimension	90x170x2000
Colour	aluminium
Material	Aluminium
Surface	Anodised
Surface standard	
Smallest sales unit	2
Unit of quantity	Metre
Weight	284.5 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	36,5408 kg CO2e / 1 Meter

Technical data sheet

Device installation trunking Rapid 80, trunking width 170, trunking height 90, asymmetrical
Item number: 6279503

Dimensions



Length	2,000 mm
Width	170 mm
Height	90 mm

Technical data

Number of covers	1
Number of insertable partitions	1
Rear panel version (inner side)	Continuous C profile
Rectangular shape	yes
Base perforation	Without base perforation
Halogen-free	yes
Cable retaining clip	no
Duct connector	no
Cover mounting type	Internal
Mounting perforation in base	no
Usable cross-section	11756 mm²
Cover supplied	no
Cover width	76.5 mm
ROHS-conformant	yes
Protection rating	IP30
Protective film	yes
Protection rating IK code	IK10
Symmetrical	no
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-25 °C