Technical data sheet

US 7 support A4

Item number: 6338876

Suspended support (U profile) with welded head plate.
For fastening to horizontal concrete ceilings and steel girders. For bracket widths of 400 mm or more, or if the bracket is mounted at the end of a suspended support, we recommend the use of the spacer, type DSK 61.

A4 Stainless steel

2B Bright, treated

Master data

Item number	6338876
Type	US 7 K 120 A4
Description 1	Support
Description 2	with welded head plate
Manufacturer	OBO
Dimension	70x50x1200
Colour	stainless steel
Material	Stainless steel 1.4571
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	578 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	33,7391 kg CO2e / 1 Piece

Technical data sheet

US 7 support A4

Item number: 6338876

Dimensions



Length	1,200 mm
Width	70 mm
Height	50 mm

Technical data

Version for	U profile
Maintain electrical functions	no
Material thickness	4 mm
Maximum tensile load	11 kN
ROHS-conformant	yes

Technical data sheet

US 7 support A4

Item number: 6338876

Loads



Load diagram, U support, type US 7 K VA

1. Bending of the end of the suspended support at permitted bracket load
2. Permitted bracket load in kN without man load
3. Bracket length in mm

— Load curves with support lengths in mm

Characteristic anchor load values for U support, type US 7 K

Single-sided load						
	Max. load [kN]					
	Bracket width [mm]					
Anchor type	110%	210	310	410	510	610
BZ3 10x90/0-30	3.97	3.03	2.44	2.04	1.76	1.54
BZ3 12x110/0-35	5.16	3.90	3.15	2.64	2.27	1.99

Max. total load F = cable weight + cable tray + bracket + suspended support. The tabular values for double-sided loads take the available axis spacing ai = 10 cm into account. The stated values are based on uncracked concrete of compressive strength C20/25. Please comply with the installation conditions of ETA(anchors).