# Technical data sheet

## US 5 support A4

## Item number: 6341055

U support in fixed lengths. Dimensions 50 x 50 mm.
For bracket widths of 400 mm or more, or if the bracket is mounted at the end of a suspended support, we recommend the use of the spacer, type DSK 45.

US5

A4 Stainless steel

2B Bright, treated

### Master data

| | |
|---|---|
| Item number | 6341055 |
| Type | US 5 40 A4 |
| Description 1 | U support |
| Description 2 | 3-sided perforated |
| Manufacturer | OBO |
| Dimension | 50x50x400 |
| Colour | stainless steel |
| Material | Stainless steel 1.4571 |
| Surface | Bright, treated |
| Surface standard | |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 97 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 5,4544 kg CO2e / 1 Piece |

# Technical data sheet

## US 5 support A4

## Item number: 6341055

### Dimensions




| | |
|---|---|
| Dimension | 50 x 50 x 2,5 |
| Length | 400 mm |
| Width | 50 mm |
| Height | 50 mm |

# Technical data sheet

## US 5 support A4

## Item number: 6341055

### Technical data

| | |
|---|---|
| Breakable | no |
| Type of perforation | 3 sides perforated |
| Version for | Single profile |
| Maintain electrical functions | no |
| Material thickness | 2.5 mm |
| With toothing | no |
| Profile shape | U profile |
| ROHS-conformant | yes |
| Static value A | 2.74 $cm^2$ |
| Static value Iy | 8.32 $cm^4$ |
| Static value Iz | 12.53 $cm^4$ |
| Static value Wy | 2.61 $cm^3$ |
| Static value Wz | 5.01 $cm^3$ |