Technical data sheet

US 5 support A2

Item number: 6341125

U support in fixed lengths. Dimensions 50 x 50 mm.
For bracket widths of 400 mm or more, or if the bracket is mounted at the end of a suspended support, we recommend the use of the spacer, type DSK 45.

US5

A2	Stainless steel
2B	Bright, treated

Master data

Item number	6341125
Type	US 5 80 A2
Description 1	U support
Description 2	3-sided perforated
Manufacturer	OBO
Dimension	50x50x800
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	193 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	11,706 kg CO2e / 1 Piece

Technical data sheet

US 5 support A2

Item number: 6341125

Dimensions



Dimension	50 x 50 x 2,5
Length	800 mm
Width	50 mm
Height	50 mm

Technical data sheet

US 5 support A2

Item number: 6341125

Technical data

Breakable	no
Type of perforation	3 sides perforated
Version for	Single profile
Maintain electrical functions	no
Material thickness	2.5 mm
With toothing	no
Profile shape	U profile
ROHS-conformant	yes
Static value A	2.74 cm^2
Static value Iy	8.32 cm^4
Static value Iz	12.53 cm^4
Static value Wy	2.61 cm^3
Static value Wz	5.01 cm^3