Technical data sheet

US 7 support A4

Item number: 6341804

U support in fixed lengths. Dimensions 70 x 50 mm.
For bracket widths of 400 mm or more, or if the bracket is mounted at the end of a suspended support, we recommend the use of the spacer, type DSK 61.

A4 Stainless steel

2B Bright, treated

Master data

Item number	6341804
Type	US 7 90 A4
Description 1	U support
Description 2	3-sided perforated
Manufacturer	OBO
Dimension	70x50x900
Colour	stainless steel
Material	Stainless steel 1.4571
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	363 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	21,7148 kg CO2e / 1 Piece

Technical data sheet

US 7 support A4

Item number: 6341804

Dimensions



Dimension	70 x 50 x 4
Length	900 mm
Width	70 mm
Height	50 mm



Technical data sheet

US 7 support A4

Item number: 6341804

Technical data

Breakable	no
Type of perforation	3 sides perforated
Version for	Single profile
Maintain electrical functions	no
Hole width	14 mm
Material thickness	4 mm
With toothing	no
Profile shape	U profile
ROHS-conformant	yes
Slot width	40 mm
Static value A	4.59 cm^2
Static value Iy	13.79 cm^4
Static value Iz	36.84 cm^4
Static value Wy	4.11 cm^3
Static value Wz	10.53 cm^3