# Technical data sheet

## US 3 support A2

## Item number: 6342463

U support in fixed lengths. Dimensions 30 x 50 mm.
For bracket widths of 400 mm or more, or if the bracket is mounted at the end of a suspended support, we recommend the use of the spacer, type DSK 25.

| | |
|---|---|
| A2 | Stainless steel |
| 2B | Bright, treated |

### Master data

| | |
|---|---|
| Item number | 6342463 |
| Type | US 3 150 A2 |
| Description 1 | U support |
| Description 2 | 3-sided perforated |
| Manufacturer | OBO |
| Dimension | 50x30x1500 |
| Colour | stainless steel |
| Material | Stainless steel 1.4301 |
| Surface | Bright, treated |
| Surface standard | |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 198 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 11,7573 kg CO2e / 1 Piece |

# Technical data sheet

## US 3 support A2

## Item number: 6342463

### Dimensions




| | |
|---|---|
| Dimension | 30 x 50 x 2,0 |
| Length | 1,500 mm |
| Width | 50 mm |
| Height | 30 mm |

# Technical data sheet

## US 3 support A2

## Item number: 6342463

### Technical data

| | |
|---|---|
| Breakable | no |
| Type of perforation | 3 sides perforated |
| Version for | Single profile |
| Maintain electrical functions | no |
| Material thickness | 2 mm |
| With toothing | no |
| Profile shape | U profile |
| ROHS-conformant | yes |
| Static value A | 1.42 $cm^2$ |
| Static value Iy | 1.52 $cm^4$ |
| Static value Iz | 5.72 $cm^4$ |
| Static value Wy | 0.7 $cm^3$ |
| Static value Wz | 2.29 $cm^3$ |