Technical data sheet

Support bracket AS 30

Item number: 6419388

Medium-duty support bracket for infinitely adjustable fastening on IS 8 support. The support bracket can be fastened to both sides of the I support.

The individual clamping lug, including bolt, nut and washer can also be ordered separately under the item no. 6419007.

St Steel

FT Hot-dip galvanised

Master data

Item number	6419388
Type	AS 30 31 FT
Description 1	Support bracket
Description 2	for IS 8 support
Manufacturer	OBO
Dimension	B310mm
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	73 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,6988 kg CO2e / 1 Piece

Technical data sheet

Support bracket AS 30

Item number: 6419388

Dimensions





Length	41 mm
Width	310 mm
Height	80 mm
Dimension A	41 mm
Dimension B	310 mm
Dimension H	80 mm

Technical data

Version for	Support bracket
F in kN	3 kN
Maintain electrical functions	no
ROHS-conformant	yes
Rustproof steel, pickled	no

Loads



Load diagram, bracket type AS 30

1. Bending of the bracket tip at permitted bracket load
2. Permitted bracket load in kN without man load

—— Load curve with bracket lengths in mm