Technical data sheet

PYROPLUG® MagicBox, three-sided, interior height 60 mm

Item number: 7204042

Fire protection box as insulation system, made of single-part stainless steel housing with intumescent fire protection inlays. Can be used in walls, on raw floors, beneath system floors and as insulation of rising sections in ceilings. Interior can be fully assigned with installations. For interior application. Closure of the residual openings with PYROSIT® NG fire protection foam, particularly simple for difficult geometries. CE-labelled construction product with general type approval. Fire resistance class EI90 (fire-resistant). Including graphite strip.

CE

A2	Stainless steel
2B	Bright, treated

Master data

Item number	7204042
Type	PMB 640-3 A2
Description 1	Fire Protection Box 3-sided
Description 2	with intumescending inlays
Available from	04.10.2022
Manufacturer	OBO
Dimension	300x423x116
Colour	stainless steel
Material	Stainless steel 1.4301
Surface Surface standard	Bright, treated
Smallest sales unit	1
Unit of quantity	Piece
Weight	383.1 kg
Weight unit	kg/100 pc.

Technical data sheet

PYROPLUG® MagicBox, three-sided, interior height 60 mm

Item number: 7204042

Dimensions



Length	300 mm
Width	423 mm
Height	116 mm
Dimension d	405 mm
Dimension d min.	423 mm

Technical data

Fire protection version	Box body
Shape	Rectangular
ROHS-conformant	yes
Accessories required	yes
Internal height	65 mm
Internal width	405 mm