Technical data sheet

Rising vertical bend EI90 for PLCS D090810 fire protection duct

Item number: 7217930

Vertical bend, rising, for PYROLINE® Con S EI90 fire protection duct, type PLCS D090810, consisting of fibreglass light concrete which is resistant to water and frost for the creation of vertical changes of direction (45°) of the duct. Mounted connectors ensure quick mounting in situ, whilst loosely placed covers ensure quick inspection and reassignment.

Including connection screws and sealing strips.
Including connection screws and sealing strips.

CE

Fibreglass lightweight concrete

Master data

Item number	7217930
Type	PLCS VR090810
Description 1	Vertical bend rising EI90
Description 2	for PLCS D090810
Manufacturer	OBO
Dimension	100x80
Colour	Grey
Material	Fibreglass lightweight concrete
Smallest sales unit	1
Unit of quantity	Piece
Weight	950 kg
Weight unit	kg/100 pc.

Dimensions



External dimensions	248 x 190
Internal dimensions	100 x 80
Dimension B	248 mm
Dimension b	100 mm
Dimension h	80 mm
Dimension H	190 mm
Dimension L	225 mm

Technical data sheet

Rising vertical bend EI90 for PLCS D090810 fire protection duct

Item number: 7217930

Technical data

Number of flammable sides	4
Cover fastening	Loose
Classification EI − installation duct	90
With perforation	no
ROHS-conformant	yes
Jacketing	Without
Material of the insulation	Glass-fibre lightweight concrete
Angle of the bend	45 °