Technical data sheet

UDHOME-ONE floor socket, without floor covering recess, freely equippable, brass, decorative plate: marygold
Item number: 7368224

Square floor socket for use in dry-care systems and screed floors in indoor areas. Installation housing with pre-marked insertion openings for pipes (M20/M25). Cover adjustable to top edge of floor covering using four height-adjustment supports. The minimum installation depth is 75 mm, the height-adjustment range +30 mm. Frame and cover made of brass and visible in the floor covering. Cover with decorative plate marygold. Empty housing for a 45® installation device and a data socket. When delivered, the item is closed with a blanking plate.

Master data

Item number	7368224
Type	UDHOME-ONE GM D1
Description 1	Floor socket
Description 2	unequipped, Marygold
Manufacturer	OBO
Dimension	140x140x75
Smallest sales unit	1
Unit of quantity	Piece
Weight	220 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	9,3489 kg CO2e / 1 Piece

Technical data sheet

UDHOME-ONE floor socket, without floor covering recess, freely equippable, brass, decorative plate: marygold
Item number: 7368224

Dimensions





Length	140 mm
Width	140 mm
Height	75 mm

Technical data

Number of installable devices	2
Cover version	Square
Cable outlet version	Swivellable cord outlet
Equipment	Empty housing
Floor covering protection frame	no
Floor care	Dry
Cover version	Decorative plate sample
Seal installation option	no
Application when used	6.101.1 Dry floor care
Application when unused	6.101.1 Dry floor care
Floor height, max.	105 mm
Floor height, min.	75 mm
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	no
Suitable for cavity floor installation	yes
Suitable for wet care	no
Suitable for underfloor ducts	no
Device support to accept mounting boxes	no
With floor covering recess	no
ROHS-conformant	Exempt
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK10
Heavy-duty version	no
Vertical load, large area	to 15,000 N
Vertical load, small area	to 3,000 N
Approvals	VDE

Technical data

Opening mechanism	Handle