Technical data sheet

Underfloor duct, 2 pieces, 2-compartment, duct height 28 mm

Item number: 7400265

Underfloor duct (2 piece) for routing cables in screed-covered underfloor systems, according to EN 50085-2-2. Removable and continuously lockable trunking cover. With separating retainers in the trunking base. Maximum load-bearing capacity to 1.5 kN.
The profiled side walls offer a locking mechanism to lock the duct cover onto the duct base. The stiffening beads in the duct cover serve to create stability.

St Steel

FS Strip galvanised

Master data

Item number	7400265
Type	S2 25028-2
Description 1	Underfloor duct, 2-part
Description 2	2 compartments
Manufacturer	OBO
Dimension	2000x250x28
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	2
Unit of quantity	Metre
Weight	369.106 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	8,1488 kg CO2e / 1 Meter

Technical data sheet

Underfloor duct, 2 pieces, 2-compartment, duct height 28 mm

Item number: 7400265

Dimensions



Length	2,000 mm
Width	250 mm
Height	28 mm
Dimension a	110 mm
Dimension b	140 mm
Dimension h	28 mm

Technical data

Number of fixed partitions	1
Number of compartments	2 St.
Mounting system fastening type	Floor
Floor plate	yes
Application area	Screed-covered
Decouplable	no
Trunking width, min.	250 mm
Duct height, min.	28 mm
Usable cross-section	6184 mm²
Removable cover	yes
Cross-section, draw a	2701 mm²
Cross-section, draw b	3483 mm²
ROHS-conformant	yes
Vertical load, large area	to 1,500 N