Technical data sheet

UTC4 W with 3+1 protective contact sockets

Item number: 7404621

The ready-for-connection UTC4 universal support has 3 pre-installed 33° protective contact sockets in white and one pre-installed 33° protective contact socket in orange, 250 V~, 16 A. With halogen-free connection cable. Suitable for VL connection cables and device installation units of nominal size R7, R9 and 9.

PVC connection cable with connector, 3-pin, type WINSTA® MIDI.

PA Polyamide

Master data

Item number	7404621
Type	UTC4 W W3OR1
Description 1	Universal supportConnectWINSTA
Description 2	triple white,single orange
Manufacturer	OBO
Dimension	208x76x45
Material	Polyamide
Smallest sales unit	1
Unit of quantity	Piece
Weight	46.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,3346 kg CO2e / 1 Piece

Technical data sheet

UTC4 W with 3+1 protective contact sockets

Item number: 7404621

Dimensions





Length	218 mm
Width	76 mm
Height	60 mm

Technical data

Connection cable, halogen-free	no
Number of installable devices	4
Version for	Triple pure white/single pure orange
Cable length	300 mm
Line cross-section	2.5 mm²
ROHS-conformant	yes
Plug-in system	WINSTA® MIDI
Plug connector system, system-specific	yes
Circuit	2
System length	208 mm
Surge protection	no