Technical data sheet

On-floor installation trunking, trunking height 40 mm

Item number: 7404700

On-floor trunking base, 1 compartment, for blank/mounting lid with slope on one side, with plug-fit aluminium side profiles for layering and fixing the trunking lid, metal floor base with holding shackles for max. two plug-in, self-contacting dividers and groove for earth conductor clamp. Trunking height suitable for installation of Telitanks.

St	Steel
FS	Strip galvanised

Master data

Item number	7404700
Type	AIKU 15040
Description 1	Trunking base
Manufacturer	OBO
Dimension	2400x150x40
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	2.4
Unit of quantity	Metre
Weight	234.3 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	11,1313 kg CO2e / 1 Meter

Technical data sheet

On-floor installation trunking, trunking height 40 mm

Item number: 7404700

Dimensions



Length	2,400 mm
Width	150 mm
Height	40 mm
Plate thickness, base	1 mm
Dimension B	150 mm
Dimension b	150 mm
Dimension h	40 mm

Technical data

Number of insertable partitions	2
Number of compartments	3 St.
Suitable for	Cover sloping on one side
With separating retainer	no
Usable cross-section	45 cm²
Cross-section, draw 3	1771 mm²
Cross-section, draw a	1630 mm²
Cross-section, draw b	1120 mm²
ROHS-conformant	yes
Separating retainer fastening	stecken
Separating retainer fastening	Plug