Technical data sheet

Service outlet with hinged cover and cord outlet, GES R2

Item number: 7405082

Service outlet with hinged cover and cord outlet for GES R2 floor socket for direct installation in the MT R2 installation socket.

For use in dry-cleaned floors for indoor use.

PA Polyamide

Master data

Item number	7405082
Type	GES R2 7011
Description 1	Floor socket
Description 2	with cord outlet
Manufacturer	OBO
Dimension	140x140x40
Colour	Iron grey; RAL 7011
Material	Polyamide
Smallest sales unit	1
Unit of quantity	Piece
Weight	8.8 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,2625 kg CO2e / 1 Piece

Technical data sheet

Service outlet with hinged cover and cord outlet, GES R2

Item number: 7405082

Dimensions



Technical data

Cable outlet version	Swivellable cord outlet
Floor covering protection frame	yes
Floor care	Dry
Suitable for raised floor installation	yes
Suitable for cavity floor installation	yes
Suitable for wet care	no
Suitable for underfloor ducts	no
With floor covering recess	no
ROHS-conformant	yes
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK10
Vertical load, small area	to 500 N
Approvals	VDE
Opening mechanism	Tool