Technical data sheet

Service outlet with blanking cover and opening contour, GES R2

Item number: 7405086

Service outlet with blanking cover and opening contour for GES R2 floor socket for direct installation in the MT R2 installation socket.

For use in dry-cleaned floors for indoor use.

PA Polyamide

Master data

Item number	7405086
Type	GES R2B 7011
Description 1	Floor socket
Description 2	Plastic
Manufacturer	OBO
Dimension	140x140x40
Colour	Iron grey; RAL 7011
Material	Polyamide
Smallest sales unit	1
Unit of quantity	Piece
Weight	8.15 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,4501 kg CO2e / 1 Piece

Technical data sheet

Service outlet with blanking cover and opening contour, GES R2

Item number: 7405086

Dimensions





Technical data

Cover version	Round
Cable outlet version	No cable outlet
Floor covering protection frame	yes
Floor care	Dry
Suitable for raised floor installation	yes
Suitable for cavity floor installation	yes
Suitable for wet care	no
Suitable for underfloor ducts	no
With floor covering recess	no
Standard	EN 50085-2-2
ROHS-conformant	yes
Protection rating (IP) when unused	IP40
Protection rating IK code	IK10
Vertical load, small area	to 500 N
Approvals	VDE
Opening mechanism	Tool