Technical data sheet

Frame cassette for cord outlet, RKS, nominal size 350-3, stainless steel
Item number: 7406534



Frame cassette for cord outlet, for UZD350-3, for the installation of accessories in dry or wet-cleaned floors for indoor use.

A2 Stainless steel

Master data

Item number	7406534
Type	RKS V3 25
Description 1	Frame cassette
Description 2	for cord outlet
Manufacturer	OBO
Dimension	383x383x25
Material	Stainless steel 1.4301
Smallest sales unit	1
Unit of quantity	Piece
Weight	763.2 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	31,1418 kg CO2e / 1 Piece

Dimensions



Dimension A	424 mm
Dimension B	388 mm
Dimension C	382 mm
Dimension h	25 mm

Technical data sheet

Frame cassette for cord outlet, RKS, nominal size 350-3, stainless steel
Item number: 7406534

Technical data

Number of cable outlets	1
Cable outlet version	Swivellable cord outlet
Floor care	Dry
Suitable for	Underfloor socket structure
Suitable for underfloor box	350
Device support to accept mounting boxes	no
ROHS-conformant	yes
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Vertical load, large area	to 3,000 N
Vertical load, small area	to 3,000 N
Floor covering thickness	23 mm