Technical data sheet

ZES6 inspection cover

Item number: 7406749



Junction box insert for blank closing of a rectangular mounting opening of nominal size 6 in an underfloor duct or trunking system or in raised floor for indoor use. Polyamide floor covering profile.

Recess is 5 mm, if necessary, adjustable to 3, 8 or 10 mm.

PA Polyamide

Master data

Item number	7406749
Type	ZES6-2 U10T 7011
Description 1	Junction box insert
Description 2	for universal mounting
Manufacturer	OBO
Colour	Iron grey; RAL 7011
Material	Polyamide
Smallest sales unit	1
Unit of quantity	Piece
Weight	150 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	4,3626 kg CO2e / 1 Piece

Technical data sheet

ZES6 inspection cover

Item number: 7406749

Dimensions



Length	221 mm
Width	274 mm
Height	65 mm

Technical data

Cover version	Rectangular
Floor covering protection frame	yes
Floor care	Dry
Floor height, min.	62 mm
Suitable for raised floor installation	yes
Suitable for cavity floor installation	no
Suitable for wet care	no
Suitable for underfloor box	250/350
Suitable for underfloor ducts	yes
Length of installation dimensions	201 mm
Nominal size for device installation units	6
Frame version	Carpet protection frame
ROHS-conformant	yes
Clamping range D, max.	75 mm
Clamping range D, min.	8 mm
Vertical load, large area	to 3,000 N
Vertical load, small area	to 2,000 N
Floor covering thickness	5 mm
Floor covering thickness max.	10 mm