Technical data sheet

Mounting support, 2 x type B

Item number: 7407842

Mounting support to accept two data connection modules of the following types BTR: E-DAT; Dätwyler: MS and MS-N; Kerpen: VarioKeystone.
Dimensions of a mounting opening in mm: 19.35/21.55 x 14.85.
Suitable for GE2F installation unit with tube body.



A2 Stainless steel

Master data

Item number	7407842
Type	MTGE2F 2B
Description 1	Mounting plate for GE2F
Description 2	with 2x hole pattern Type B
Manufacturer	OBO
Material	Stainless steel 1.4301
Smallest sales unit	1
Unit of quantity	Piece
Weight	0.26 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,276 kg CO2e / 1 Piece

Technical data sheet

Mounting support, 2 x type B

Item number: 7407842

Dimensions





Length	108 mm
Width	108 mm

Technical data

Number of installable devices	2
Number of strain reliefs	0
Version for	Support shape
Fastening type	Lockable
Labelling panel	no
Floor covering protection frame	no
Floor plate	no
Lowerable to be flush-floor	no
Seal installation option	no
Installation opening for on-floor tank	no
Decouplable	no
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	yes
Suitable for screed-covered underfloor ducts	yes
Suitable for cavity floor installation	yes
Suitable for underfloor ducts	yes
With floor covering recess	no
Accessory mounting type	Bolts
ROHS-conformant	yes
Heavy-duty version	no
Depth	14 mm
Strain relief option	yes