# Technical data sheet

## Cover plate, Telitank T12L, Modul 45® installation opening

## Item number: 7408148

Cover plate with rectangular opening for a Modul 45 accessory, suitable for lengthwise side of T12L (1/4 cover) or for T12L narrow side (1/2 cover).

PA Polyamide

### Master data

| | |
|---|---|
| Item number | 7408148 |
| Type | T12L P15S 9011 |
| Description 1 | Cover plate |
| Description 2 | for 1-way Modul 45 in T12L |
| Manufacturer | OBO |
| Dimension | 71x88x12 |
| Colour | Graphite black; RAL 9011 |
| Material | Polyamide |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 1.4 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,074 kg CO2e / 1 Piece |

# Technical data sheet

## Cover plate, Telitank T12L, Modul 45® installation opening

## Item number: 7408148

### Dimensions




| | |
|---|---|
| Length | 88 mm |
| Width | 71 mm |
| Height | 2 mm |

### Technical data

| | |
|---|---|
| Application | On-floor tank |
| Number of CEE/Perilex openings | 0 |
| Number of triple openings | 0 |
| Number of single openings | 1 |
| Number of oval openings | 0 |
| Number of square openings | 0 |
| Number of round openings | 0 |
| Number of double openings | 0 |
| Fastening type | Screw-on |
| Labelling panel | no |
| Blanking lid | no |
| Seal installation option | no |
| Suitable for labelling panel | no |
| Installation technology | Grid M45 |
| ROHS-conformant | yes |